



Series
RM

Rate-Master® Flowmeters

Polycarbonate, Gas Flow from .1-1800 SCFH, Water Flows to 10 GPM


Flow



Model RMC-SSV10®
scale, 15" high

Model RMB-SSV 5"
scale, 8" high

Model RMA-SSV 2"
scale, 4½" high



DIMENSION IN INCHES			
	Model RMA	Model RMB	Model RMC
A	4 ¹ / ₆	8 ¹ / ₂	15 ¹ / ₂
B	3 ½ NPT Conn.	6 ¹ / ₆ ¼ NPT Conn.	12 ¹ / ₄ ½ NPT Conn.
C	1 ¹ / ₆ 10-32 Thds.	3 ⁵ / ₆ ¼-20 Thds.	8 ¹ / ₆ ¾-24 Thds.
D	¾	5 ¹ / ₆	1
E	1 ¹ / ₆	1 ¹ / ₆	2 ¹ / ₄
F	1 ¹ / ₆	1 ¹ / ₄	2 ¹ / ₄
G	¾	1	1 ¹ / ₆
H	1	1 ¹ / ₆	1 ³ / ₂
I (OPEN)	1 ¹ / ₆	1 ¹ / ₆ (BV or SSV MODELS ONLY)	2 ¹ / ₂
J	¾	1 ¹ / ₆	2
K	4 ³ / ₆	8 ¹ / ₆	15 ¹ / ₂
L	1	1 ¹ / ₆	2 ¹ / ₄

The Rate-Master® flowmeter line of direct reading precision flowmeters incorporates many unique user features at moderate cost. These low cost flowmeters are ideal for general use.

Easy to read design – The direct reading scales eliminate troublesome conversions. The scales are brushed aluminum, coated with epoxy and the graduations are on both sides of the indicating tube. Special integral flow guides stabilize the float throughout the range to keep it from hunting or wandering in the bore. The float is highly visible against a white background.

Construction assures accuracy – All Rate-Master® flowmeter bodies are injection molded of tough, clear, shatter-proof polycarbonate plastic around a precision tapered pin. The result is accurate and repeatable readings. The single piece plastic body is mounted to a stainless steel back bone into which pipe thread inserts are welded to absorb piping torque. Precision metering valves of brass or stainless steel (specify BV or SSV on order) are available as an optional extra and permit precise flow adjustments. For vacuum applications, Model RMA units are available with top mounted valves (specify TMV). The small Series RMA models are accurate within ±4% of full scale reading; Series RMB within ±3%; large Series RMC within ±2%.

Installation is simple – The Rate-Master® Flowmeter can be neatly panel mounted to keep flow tube centers in the same plane as the panel surface or surface mounted on the panel by means of tapped holes in the backbone. When through-panel mounted, the bezel automatically positions the instrument at the correct depth in the panel cutout. Surface mounted units can also be held in place by the piping. All mounting hardware plus installation and operating instructions are included.

Easy-to-Interchange bodies – Within a given Series Rate-Master® flowmeter bodies can be instantly interchanged. Simply “unplug” the body from backbone and replace it with another. “O” rings provide a tight seal on inlet and outlet. Piping remains undisturbed. Interchangeability is useful where different scale ranges are sometimes required at the same location in the laboratory or plant.

Cleaning is easy – To release the plastic flowmeter body from the stainless steel backbone, just remove four screws. Pipe thread flow connections remain undisturbed. Remove the slide cover and the plug ball stop, clean the flow tube with soap and water and reassemble. It's that simple.

How To Order

Series-Range No.-Valve-Option

Example: RMA-2-SSV

Series RMA with .1-1 SCFH Air Range & Stainless Steel Valve

Model RMA

RMA-X, Standard RMA

RMA-X-BV, RMA with Brass Valve

RMA-X-SSV, RMA with Stainless Steel Valve

RMA-X-TMV, RMA with Top Mounted Valve

Model RMB

RMB-X, Standard RMB

RMB-X-BV, RMB with Brass Valve

RMB-X-SSV, RMB with Stainless Steel Valve

Model RMC

RMC-X, Standard RMC

RMC-X-BV, RMC with Brass Valve

RMC-X-SSV, RMA with Stainless Steel Valve

SPECIFICATIONS

Service: Compatible gases and liquids.

Wetted Materials: Body: Polycarbonate

O-ring: Neoprene & Buna-N.

Metal Parts: Stainless Steel (except for optional brass valve).

Float: Stainless steel, black glass, aluminum, K monel, tungsten carbide depending on range.

Temperature Limit: 130°F (54°C).

Pressure Limit: 100 psi (6.9 bar).

Accuracy: RMA: 4%, RMB: 3%, RMC: 2% of full scale.

Process Connection: RMA: 1/8", RMB: 1/4",

RMC: 1/2" female NPT.

Weight: RMA: 4 oz (113.4 g), RMB: 13 oz (368.5 g),

RMC: 39 oz (1105.6 g).

CAUTION

Dwyer® Rate-Master® flowmeters are designed to provide satisfactory long term service when used with air, water, or other compatible media. Refer to factory for information on questionable gases or liquids. Caustic solutions, anti-freeze (ethylene glycol) and aromatic solvents should definitely not be used.

OPTIONS & ACCESSORIES



Adjustable pointer flags – Red lined pointer flags provide quick visual reference to a required flow level. Of clear plastic, they snap into place inside bezel and slide to desired level.



Top Mounted Metering Valves – Same precision construction for vacuum applications. RMA models only.

Specials — Special ranges, scales, mounting arrangements, etc., are available on special order, or in OEM quantities.

RMA-X-APF, Adjustable Pointer Flag for RMA Series
 RMB-X-BPF, Adjustable Pointer Flag for RMB Series
 RMC-X-CPF, Adjustable Pointer Flag for RMC Series

RKA, Regulator Kit for RMA Series

RK-RMB, Regulator Kit for RMB Series

POPULAR RANGES

Model RMA-2" Scale		Model RMB-5" Scale		Model RMC -10" Scale	
Range SCFH Air	Range No.	Range SCFH Air	Range No.	Range SCFH Air	Range No.
.05-.5	1	.5-5	49	5-50	101
.1-1	2	1-10	50	10-100	102
.2-2	3	3-20	51	20-200	103
.5-5	4	4-50	52	40-400	104
1-10	5	10-100	53	60-600	105
2-20	6	20-200	54	100-1000	106
5-50	7	40-400	55	120-1200	107
10-100	8	50-500	56	200-1800	108
15-150	9	60-600	57		
20-200	10			SCFM Air	
		Gal. Water per hour		1-10	121
CC Air/min.				2-20	122
5-50	151*	1-12	82	4-30	123
10-100	150*	1-20	83		
30-240	11	4-40	84	Gal. Water per hour	
50-500	12	10-100	85		
100-1000	13	SCFH & LPM Air		2-20	134
200-2500	14	1.2-10/0.6-5	50D	8-90	135
LPM Air		3-20/1.5-9.5	51D		
.5-5	26	4-50/2-23	52D	Gal. Water per minute	
1-10	21	10-100/5-50	53D	.1-1	141
2-25	22	20-200/5-95	54D	.2-2.2	142
5-50	23	GPH & LPM Water		.4-4	143
5-70	24	1-12/0.06-0.76	82D	.8-7	144
10-100	25	1-20/0.065-1.25	83D	1.2-10	145
CC Water/min.		10-100/0.8-6.2	85D		
5-50	32				
10-110	33				
20-300	34				
Gal. Water/hr					
1-11	42				
2-24	43				
4-34	44				
5-50	45				

*Accuracy ±8%
 +Accuracy ±5%